



SIDE MOUNT, FLAT BASE, POST-TYPE INSULATOR BRACKET, 9-1/2in POLE OFFSET

By Hubbell
Catalog # [PSC2060717](#)

Bracket mounts post-type insulators to side of pole in horizontal position with 15 degree up sweep. Lineman's slang is chicken wing.

Features

- Mounts to pole with 5/8" dia. through bolt
- Accepts 7/8" dia. insulator line post stud
- Includes hole for stringing block
- Material: 3/8" x 4" galvanized steel per ASTM A-153

General

Coating	Galvanized, ASTM A-153
Material	Steel
Style	Flat Back
Type	Bracket
UPC	096359514442



*Representative Image

Dimensions

Distance From Pole	9.5 in
Weight	12.17 lb

Product Assets

[Sales Drawings - Mounting Bracket \(SA2060717\)](#)
[Technical Solutions - CH-PSC2060717-SPEC-EN](#)
[Test Documents - Capacity Chart for PSC2060706_PSC2060717](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CH-PSC2060717-SPEC-EN | REV 1/2024