



## Klik Pin, 0.187 X 1.562 in

By Chance Lineman Tools & Equipment  
Catalog # [059738P](#)

Klix Pin.



\*Representative Image

### Features

- Tested per OSHA & ASTM F711
- For many transmission and EHV maintenance applications
- Help support conductors while insulators are removed and replaced
- Used with yoke plates and hook assemblies at the conductor
- Also used for structure ends of suspension, V-string or deadend insulator strings
- 5 stainless-steel crosspins are located at 6" intervals on the 2"-diameter Epoxiglas™ poles to support hot-end trunnions or hooks
- Engaging deadend and suspension yokes at the hot end also require the adjustable, heat-treated aluminum pole clamp
- Pole clamp can be unlocked and positioned by hotsticks
- On cold end, a high-strength steel strain-jack with bronze tongue provides take-up with a ratchet wrench (see page 2257) and trunnions (page 2255) (Wrench and trunnions must be ordered as separate items)
- Standard strain jack included with each strain pole provides 12" of adjustment

### General

Style Accessories  
UPC 096359215431

### Dimensions

Weight 0.1 lb  
WeightMetric 0.0 kg

### Product Assets

[Literature - Transmission Project Tools and Equipment Checklist \(CENT\\_LTE\\_FRM\\_EN\\_00082\)](#)

### Related Products

- [C4012146 - Adjustable Strain Pole, 8 ft \(2.4 m\), 5 Pins](#)
- [C4012145 - Adjustable Strain Pole, 6 ft \(1.8 m\), 5 Pins](#)
- [C4012147 - Adjustable Strain Pole, 10 ft \(3.0 m\), 5 Pins](#)
- [C4012144 - Adjustable Strain Pole, 6 ft \(1.8 m\), 5 Pins](#)
- [C4012149 - Adjustable Strain Pole, 18 ft \(5.4 m\), 5 Pins](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CLTE-059738P-SPEC-EN | REV 1/2024