

Snatch Block with Forged Steel Hook, 1,250 lb.

By Chance Lineman Tools & Equipment
Catalog # [22301](#)

Light-weight cast-aluminum housing and sheave with a hinged cotterlock yoke and forged steel hook makes for quick rigging in diversified applications.



Features

- Spring Loaded safety latch on forged steel hook
- Sheave operates on bronze oilite bearings
- Maximum rope size is 5/8"
- Maximum rated working load 1,250 lb.
- Replacement Ball Lok pin and chain PS400006 available separately

General

EU RoHS Indicator	No
Material	Cast Aluminum
Max Load Lbs.	1250 lb
Style	With Steel Hook
Swivel Top?	Yes
Type	Load Lift Assist
UPC	096359069775

Dimensions

Weight	2 lb
WeightMetric	0.9 kg

Logistics

Pallet Quantity	300
Standard Package	1

Product Assets

[Catalogs - Load Handling Accessories](#)
[Installation Manuals - CHANCE Snatch Block 22301 ENG](#)