



Barry D.E.W. Line® Work Rope, 50 ft/15.2 m

By CHANCE Utility
Catalog # [PSCDEWNP28050](#)

Dielectric Even Wet insulating rope tool designed for performing live line work on AC or DC systems.



Features

- Rated Working Load 1,260 lb./571.5 kg
- Meets or exceeds dry or wet electrical requirements of IEC 62196:2009 and ASTM F1701-12
- Cleanable and easy to maintain and test
- Arc-Flash Category 4 rated
- Fixed length with stainless steel thimbles and sealed terminations
- Storage bag with dessicant included

General

Tensile Strength	6,300 lb./2,857 kg
UPC	096359752998
Working Load Limit	1,260 lb
Working Load Limit Metric	571 kg

Dimensions

Diameter	0.50 in
Length	50 ft
Length Metric	15.2 m
Weight	7.3 lb
WeightMetric	3.3 kg

Product Assets

[Installation Manuals - Barry D.E.W. Line Insulating Rope Equipment](#)
[Literature - CHANCE® Barry D.E.W. Line® Rethink Rope \(CENT_LTE_BR_EN_00105\)](#)
[Technical Solutions - CH-PSCDEWNP28050-SPEC-EN](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CH-PSCDEWNP28050-SPEC-EN | REV 1/2024