



APITONG WOOD CROSSARM BRACE, 1-3/4in PROFILE, 60in SPAN x 18in DROP, SOLD AS PAIR

By CHANCE Utility
Catalog # [PSCRA6018](#)

Under-arm wood crossarm braces are installed as pairs in a V-type configuration to the arm and pole face to strengthen the crossarm and provide stability. Order quantity of one pair for one V-type installation.



*Representative Image

Features

- Reversible style brace
- 9/16" dia. crossarm hole and 11/16" pole hole
- Tongue and groove fitting/wood connection captured with nail through both wood and aluminum
- End fittings are 6061-T6 aluminum
- Brace member is Apitong wood, pressure treated with copper naphthenate per AWPA P8 standards
- RUS Listed cu - Brace, crossarm, wood

General

Material	Apitong Wood w/ 6061-T6 Aluminum Fittings
UPC	096359464662

Dimensions

Distance From Pole	N/A
Length	35.00 in
Weight	7.3 lb

Certifications and Compliance

RUS Listed Reference	cu - Brace, crossarm, wood
----------------------	----------------------------

Logistics

Pallet Quantity	200
-----------------	-----

Product Assets

- [Catalogs - Aluminum Hardware & Apitong Wood \(5B\)](#)
- [Literature - Apitong Sustainability](#)
- [Sales Drawings - Reversible Apitong Brace \(SAPSCRA4814\)](#)



A proud member of the Hubbell Family.