



Bus Bar Ground Clamp with Rated Stud, Type I-Class A-Grade 7H, 6.625" Jaw Opening

By CHANCE Utility
Catalog # [PSCT6000844001](#)

Bus Bar Ground Clamp with Rated Stud, Type I-Class A-Grade 7H, 6.625" Jaw Opening



Features

- Bus-Bar Ground Clamp
- Continuous Current 400A
- Fault Current 68kA for 15 cycles X/R=30
- Main Line Range Max. 6-5/8" O.D. Bus
- Main Line Range Min. 3-1/2" O.D. Bus
- Rated 8.5" x 0.75" Stud
- ASTM Type I, Class A, Grade 7H
- Jaws Smooth
- Rated Stud

General

| | |
|-------------------------------------|--------------|
| Eye Screw/T-Handle | 300 in-lb |
| Installation Torque (in-lb) | |
| Ferrule Installation Torque (in-lb) | N/A |
| Material | Aluminum |
| UPC | 096359599623 |

Dimensions

| | |
|--------|--------|
| Weight | 7.8 lb |
|--------|--------|

Certifications and Compliance

| | |
|----------------------------|----|
| Fault Current - ASTM Grade | 7H |
|----------------------------|----|

Logistics

| | |
|-----------------|----|
| Pallet Quantity | 24 |
|-----------------|----|

Product Assets

[Catalogs - Grounding Equipment \(3000\)](#)
[Literature - ASTM H-Rated Grounding Sets, Clamps, and Ball Studs \(CENT-LTE-H-RATED-GROUNDING-BR-EN-00301_web\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-PSCT6000844001-SPEC-EN | REV 8/2023