

Fixed Strain Pole, 9 ft 5 in (2.8 m), Butt Swivel and Clevis

By Chance Lineman Tools & Equipment
Catalog # [C4000612](#)



C6010260.

Features

- Tested per OSHA & ASTM F711
- Accommodate a wide range of yoke plate designs and hole spacings
- Both Strain Poles, of 2"-dia. Epoxiglas™ construction, offer 12,000-pounds maximum load capacity with a 1" wide clevis for aluminum conductor yoke plates
- Commonly used in deadend rigging, for "V" strings and restrained angles, poles offer two clevis lengths and overall lengths

General

EU RoHS Indicator	No
Style	For Bundle Conductor Yoke Plates
UPC	096359016694
Working Load Limit	12,000 lb
Working Load Limit Metric	5,443 kg

Dimensions

Dimension - L Length Overall mm	2,870 kg
Dimension - Length Overall inch	113 in
Dimensions	120 in x 4.38 in x 4.38 in
Dimensions Metric	304.8 mm x 11.1 mm x 11.1 mm
Height	4.38 in
Height Metric	11.1 mm
Length	120 in
Length Metric	304.8 mm
Weight	14 lb
WeightMetric	6.3 kg
Width	4.38 in
WidthMetric	11.1 mm

Product Assets

[Installation Manuals - CHANCE® Tools Manuals](#)
[Literature - Transmission Project Tools and Equipment Checklist](#)



A Hubbell brand