



BOLT, DA, 7/8in x 44in, w/4 NUTS

By Hubbell
Catalog # [PSDA784400](#)



Double-arming bolts are used in pairs to "unitize" two crossarms when line construction requires the strength of double arm construction. Industry slang is D A Bolt.

Features

- Full-thread with cone pointed ends
- Includes four square nuts
- Rated tensile strength is 25,400 lbs.
- Galvanized per ASTM A-153
- Manufactured in compliance with ANSI C135.1

General

Coating	Galvanized, ASTM A-153
Material	Steel
Tensile Strength	24500 lb.
UPC	096359505013

Dimensions

Diameter	0.88 in
Diameter (Fraction)	7/8 in
Length	44.00 in
Weight	7.26 lb

Product Assets

[Sales Drawings - Double Arm Bolt \(SADA781200\)](#)
[Technical Solutions - CH-PSDA784400-SPEC-EN](#)

Related Products

[6819 - 4in SQUARE FLAT WASHER for 7/8in BOLT SIZE, 15/16in HOLE](#)
[PS6807 - WASHER, ROUND, 15/16in HOLE, 2-1/4in DIA.](#)
[680912 - 4in SQUARE CURVED WASHER for 7/8in BOLT SIZE, 15/16in HOLE](#)
[3514 - MF TYPE CURVED LOCK NUT, 7/8in THREAD](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CH-PSDA784400-SPEC-EN | REV 1/2024