



## CHANCE® Short Circuit Stick with 4 and 5 Clamps for Bare Vertical Secondary Overhead Systems (20cm spacing)

By CHANCE Utility  
Catalog # [PST6003585](#)

CHANCE® Short Circuit Stick with 4 and 5 Clamps for Bare Vertical Secondary Overhead Systems (20cm spacing)



\*Representative Image

### Features

- Short Circuit Stick with spring loaded clamps for bare vertical secondary overhead systems
- Fault current rated and tested per IEC 61230 at 3kA/1 second
- Handle meets ASTM F711 and IEC 60855
- Clamps are spring loaded and allow connection of the phases to the neutral in one swift movement
- Conductor range: Min. 3.5mm up to Max. 19.5mm diameter
- Includes 4 clamps on one side and 5 clamps on the other with 20cm vertical spacing on both sides

### Dimensions

Weight 2.1 kg

### Logistics

Standard Package 1

### Product Assets

[Catalogs - Grounding Equipment \(3000\)](#)  
[Literature - SF\\_09\\_103S - ShortCircuit Stick 2019 \(Spanish\)](#)  
[Literature - SF\\_09\\_103E - ShortCircuit Stick 2019](#)  
[Sales Drawings - Short Circuit Stick with 4 and 5 clamps - 20 cm spacing](#)  
[Video - CHANCE Temporary Protective Grounding \(VI09072SP0720\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
CH-PST6003585-SPEC-EN | REV 8/2023