



ANCHOR, SS200 10ft. W/10,12,14,14

By Chance
Catalog # [T1100809](#)

Square Shaft (SS 200) Lead Section 10' (3048 mm) long with 10" (254 mm)-12" (304 mm) - 14" (355 mm) - 14" (355 mm) Helices.

Features

- Square Shaft Lead Sections are assembled to Square Shaft Extension with through bolt.
- The helical shaped plates do not auger into the soil but rather screw into it with minimal soil disturbance
- Hot dipped galvanized per ASTM A153
- Capacity of anchor can be determined by measuring installation torque

Application

Helical Anchoring

General

Catalog Number	T1100809
Coating	Galvanized
Number of Helices	4
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	150000 lb.



Torque Rating	16000 ft-lbs
Type	Lead Sections
UPC	096359708643

Dimensions

Anchor Helix Diameter(s)	10 in - 12 in - 14 in - 14 in
Length	120 in

Product Assets

- [Catalogs - Anchor Tools](#)
- [Catalogs - Anchors](#)
- [Installation Manuals - Holding Capacity Chart - SS200 Anchors](#)
- [Installation Manuals - TD06132E_Type_SS_and_RR_Anchors](#)
- [Installation Manuals - Holding Capacity Chart - Soil Classification](#)
- [Literature - Helical Piles and Guy Anchors Structures](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance](#)
- [Literature - Square Shaft Efficient Helical Pile Design](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Specifications - T1100809](#)
- [Video - CHANCE Square Shaft Anchor Installation](#)
- [Video - CHANCE Square Shaft Anchor Tools Selection Process](#)
- [Video - Chance Foundation Solutions Anchor/Pile Installation Tools](#)



A Hubbell brand