

Double and Triple Blocks with 150 ft of 1/2 in Samson SSR-100-3 Rope

By Chance Lineman Tools & Equipment
Catalog # [C4000925](#)



Rope is pre-installed for immediate use out of the box

Features

- Shells and sheaves are made of high dielectric, fiberfilled natural nylon
- Silicon Bronze Shaft with Oil-Impregnated Bronze Sheave Bearings
- Dielectric rating in dry weather is 30,000 volts between bearing and mounting bolt nut
- Maximum rope diameter accepted is 1/2"

General

Material	Polyolefin-Polyester Blend Rope
Max Load Lbs.	3500 lb
Style	Double & Triple Blocks w/ 150' of Rope
Swivel Top?	Yes
Type	Load Lift Assist
UPC	096359016960

Dimensions

Weight	20.5 lb
WeightMetric	9.3 kg

Logistics

Pallet Quantity	24
Standard Package	1

Product Assets

[Catalogs - Load Handling Accessories](#)
[Sales Drawings - SA_C4000925](#)