



SPOOL INSULATOR DEADEND CLEVIS, SWINGING STYLE w/BRACKET and ANSI 53-1 INSULATOR

By CHANCE Utility
Catalog # [T2070110](#)

Clevis bracket for spool insulators used in secondary deadend applications. Minimum ultimate deadend strength is 2,000 lbs. Includes gray ANSI Class 53-1 spool insulator and angle bracket with 11/16" hole. Replacement components: clevis pin - P2070061; cotter pin - 056746P.



Features

- 23/64" dia. clevis pin with self-locking cotter pin
- Hot dip galvanized per ASTM A-153
- Bracket has 5/8" dia. hole for mounting
- Manufactured in compliance with ANSI/IEEE C135.20

General

Coating	Galvanized, ASTM A-153
Material	Steel
Style	Clevis & Mounting Bracket
Type	Insulated Secondary Clevis
UPC	096359057574

Dimensions

Distance From Pole	N/A
Height	2.25 in
Length	2.50 in
Weight	1.38 lb

Logistics

Pallet Quantity	600
-----------------	-----

Product Assets

[Catalogs - Pole Line Hardware](#)
[Sales Drawings - Clevis Swinging Service \(SA1948C\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-T2070110-SPEC-EN | REV 4/2023