

## Single-Pole Strain Carrier Yoke for Flat Plates up to 1 inch Thick

By Chance Lineman Tools & Equipment  
Catalog # C4011718

YOKE, DEADEND, These yokes can be used with adjustable strain poles to remove the strain from one string of multiple strings of deadend insulators. Because the yokes are designed to fit various types of yoke plates, they should be purchased in pairs to fit the specific construction. The same yoke assemblies can be used on both the hot and cold end of the insulator string as they hook into the yoke plate hardware. All of these yokes are rated at 15,000 pounds maximum load per insulator string.

### Features

- Can be used with adjustable strain poles to remove the strain from one string of multiple strings of deadend insulators
- Should be purchased in pairs to fit specific yoke plate construction
- Same yoke assemblies can be used on both the hot and cold end of the insulator string as they hook into the yoke plate hardware
- All of these yokes are rated at 15,000 lbs. maximum load per insulator string

### General

Catalog Number	C4011718
EU RoHS Indicator	No
Style	Single Pole Strain Carrier Yokes
UPC	096359017615
Yokes	Flat plates up to 1" thick



\*Representative Image

### Dimensions

Dimensions	20 in x 7 in x 10 in
Dimensions Metric	50.8 mm x 17.8 mm x 25.4 mm
Height	10 in
Height Metric	25.4 mm
Length	20 in
Length Metric	50.8 mm
Weight	16 lb
WeightMetric	7.2 kg
Width	7 in
WidthMetric	17.8 mm

### Certifications And Compliance

Buy American Compliant      Contact Manufacturer

### Product Assets

[Literature - Transmission Project Tools and Equipment Checklist Specifications - C4011718](#)