



# ARRAN X

LED Floodlight

The **Arran X** is a new, revolutionary, energy efficient floodlight designed to withstand the most industrial harsh environments, without sacrificing light quality, durability, or safety. With a robust clamshell design, including a captive swing barrel latch, that offers complete and unimpeded access to the wiring chamber, which allows for a quick and easy installation. Multiple optic types are also available, so that light distribution can be tailored to application need.

Intelligent battery backup is also available as an option which includes Self-Testing feature which runs a 30 second test every 30 days and a 90 or 180 minute test every twelve months. Bi-coloured LED indicator provides a visual fault detection and charging status. With a greater range of output and optic options the Arran X offers a complete package for all Industrial floodlight applications.

CE

International Approvals

## Mounting Options

Floodlight. Pole/Column. High Bay

## Standard Specification

Arran X LED Floodlight

Enclosure	Marine grade Copper-Free Aluminium body with standard glass diffuser. Epoxy powder finish (Grey)
Entry	2 x M20 cable entries
Termination	3 core 6mm <sup>2</sup> max. conductor with looping
Installation	Stirrup mounting bracket
Control Gear	Electronic Driver
Colour Temperature (CCT)	5000K (Cool White)
Colour Rendering Index (Ra)	>70
Maintenance	Easy Install with clamshell splice box for unimpeded wiring access. Slotted screws
Ingress Protection	IP66
Surge Protection	6kV & 4kV for 30L
Electrical Supply	120-277V AC 50/60Hz

## Features

- ◆ **Easy Install** with clamshell splice box for unimpeded wiring access
- ◆ **Front access cover** with screwless mains terminals for easy termination.
- ◆ **Optics options** including Asymmetric, Narrow and Extra Wide
- ◆ **Intelligent battery backup** with built in self-monitoring and testing
- ◆ **Light weight** at 11.3kg

Std. Cat No.	Delivered Output	Power Consumption	Ambient °C	Weight
<b>ARXI/07L/LE</b>	7407 lm	63W	-50 to +55	11.3kg
<b>ARXI/10L/LE</b>	10264 lm	91W	-50 to +55	11.3kg
<b>ARXI/14L/LE</b>	14133 lm	118W	-50 to +55	11.3kg
<b>ARXI/20L/LE</b>	18954 lm	178W	-50 to +55	11.3kg
<b>ARXI/30L/LE</b>	28423 lm	269W	-50 to +55	11.3kg
<b>ARXI/07L/LE/EM</b>	7407 lm	63W	-20 to +50	12.03kg
<b>ARXI/14L/LE/EM</b>	14133 lm	118W	-20 to +50	12.03kg

Standard fitting supplied without optics with a wide beam distribution

ARXI/07L/LE/EM 1000 lumens 90 minute emergency duration

ARXI/14L/LE/EM 1000 lumens 90 minute emergency duration

Glass lens as standard

#### Intelligent Battery Backup

- Self-diagnostics monitors LED luminaire status
- Self-Test feature automatically runs a 1 month and bi-yearly functional test
- LED indicator provides visible fault detection and charging status
- User initiated 1, or 90-minute system test feature
- 15 minute re-transfer delay
- Automatic unit transfer when there is an unintentional drop in voltage. (below 80% of nominal AC input voltage)

#### Options - Suffix to Catalogue No.

<b>/M25</b>	M25 cable entries	<b>/3H</b>	3 hour battery duration (500 lumens)
<b>/AS</b>	Asymmetric distribution	<b>/3K</b>	3000K (Warm White) LEDs
<b>/N</b>	Narrow Beam distribution	<b>/ADE</b>	Amber LED Turtle friendly*
<b>/X</b>	Extra Wide Beam distribution	<b>/DM</b>	DALI Dimmable driver**

\* only available with the 14L and 30L options

\*\* Available up to the 20L option

Optics are not available on the 30L fitting

## Accessories order separately

	Order Code
Wire Guard 316 Stainless Steel (not used with KFLX-DARK)	<b>KFLX-GUARD</b>
Anti Glare Shield Visor that blocks upward light when mounting at angles above 45° (not used with KFLX-GUARD)	<b>KFLX-DARK</b>
Pole Mounting Bracket Assembly (48-70mm Pole Diameter)	<b>S2400-0002</b>

