

# Single-Pole Strain Carrier Yoke for Flat Plates up to 3/4 inch Thick

By Chance Lineman Tools & Equipment  
Catalog # [C4011719](#)



YOKE, SINGLE FOR RECT OR TRI, These yokes can be used with adjustable strain poles to remove the strain from one string of multiple strings of deadend insulators. Because the yokes are designed to fit various types of yoke plates, they should be purchased in pairs to fit the specific construction. The same yoke assemblies can be used on both the hot and cold end of the insulator string as they hook into the yoke plate hardware. All of these yokes are rated at 15,000 pounds maximum load per insulator string.

### Features

- Can be used with adjustable strain poles to remove the strain from one string of multiple strings of deadend insulators
- Should be purchased in pairs to fit specific yoke plate construction
- Same yoke assemblies can be used on both the hot and cold end of the insulator string as they hook into the yoke plate hardware
- All of these yokes are rated at 15,000 lbs. maximum load per insulator string

### General

Catalog Number	C4011719
EU RoHS Indicator	No
Style	Single Pole Strain Carrier Yokes
UPC	096359017622
Yokes	Flat plates up to 3/4" thick

### Dimensions

Dimensions	25 in x 8.5 in x 8.5 in
------------	-------------------------

Dimensions Metric	63.5 mm x 21.6 mm x 21.6 mm
Height	8.5 in
Height Metric	21.6 mm
Length	25 in
Length Metric	63.5 mm
Weight	18 lb
WeightMetric	8.1 kg
Width	8.5 in
WidthMetric	21.6 mm

### Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

### Logistics

Carton Quantity	1
-----------------	---

### Product Assets

[Catalogs - Transmission Tools](#)  
[Literature - Transmission Project Tools and Equipment Checklist](#)  
[Specifications - C4011719](#)