

EVOLUTION X

Ex db eb LED Pendant

The next generation in Zone 1 LED luminaires, the **Evolution X** focuses on the need of the user by combining high powered performance with long term maintenance benefits. Providing a market leading photometric output up to 40,000 lumens, and offered with a variety of optics to efficiently illuminate any Zone 1/21 application, the **Evolution X** is a true successor to the traditional high output HID pendants.

With no exposed flamepaths and an expected LED L70 life >200,000 hours at the maximum rated ambient of 60°C, the robust LED enclosure is effectively maintenance free. The optional benefit of a removeable gearbox with excellent IP allows the maintainable components to be easily accessible, and ensures that the ground breaking **Evolution X** is suitable for global use in any harsh or hazardous environment.



Mounting Options

Pendant. High Bay.

Standard Specification

Evolution X Ex db eb LED Pendant			
Type of Protection	Ex db eb (Flameproof, Increased Safety) Ex tb (Dust Protected Enclosure)		
ATEX Classification	Group II Category 2 GD		
Area Classification	Zone 1 and 21 areas to EN 60079-10-1 and EN 60079-10-2 with installation to EN 60079-14		
Certificate	EU Type Examination Certificate CML20ATEX1114X IECEx Certificate of Conformity IECEx CML 20.0073X UK Type Examination Certificate CML 21UKEX1510X		
Coding	Ex db eb IIB+H2 T* Gb Ex tb IIIC T**°C Db IP6X Refer to table for T rating and Ambient		
Enclosure	LM6 Marine grade aluminium body with UV resistant glass diffuser. LED heatsink and gearbox with epoxy powder finish (RAL 7040)		
Entry	2 x M20 cable entries		
Termination	3 core 6mm ² max conductor with looping		
Installation	8 x Ø13 mounting holes stirrup		
Control Gear	Electronic Driver		
Optical Distribution	Wide beam		
Colour Temperature (CCT)	5000K (Cool White)		
Colour Rendering Index (Ra)	>80		
Maintenance	Front access to gearbox lid with 4x M6 captive screws		
LED Lifetime @ 60°C Ambient	L70 > 200,000hrs		
System Life @ Ambient	120,000hrs @ 25°C		
Impact Protection	IK10		
Ingress Protection	IP66/67 to EN 60529		
Surge Protection	6kV		
Electrical Supply	110-277V AC, 50/60Hz 127-250V DC		

Features

- Highly Energy Efficient >106lm/W
- Slimline, Sealed for life LED enclosure with no exposed flamepaths
- Easy access gearbox with captive screws
- Available with **asymmetric optic**, minimising light pollution
- **Remote gearbox** option with flying lead for ease of maintenance and installation
- 120,000 maintenance free hours at 25°C



UK / Europe / Africa / North America **T:** +44 (0)141 810 9644 E: hhsales1@hubbell.com Asia / Middle East / South America **T:** +44 (0)141 810 9666 E: hhsales2@hubbell.com



Std. Cat No.	Delivered Output	Power Consumption	Tclass	T°C (Dust)	Ambient °C	Weight
EVXB/20L/LE/PE	20,980 lm	188W	T5 T4	T100 T135	-55 to +40 -55 to +60	15.5kg
EVXB/30L/LE/PE	29,433 lm	253W	T5 T4	T100 T135	-55 to +40 -55 to +60	17kg
EVXB/40L/LE/PE	40,052 lm	375W	T5 T4	T100 T135	-55 to +40 -55 to +60	17kg

Options - Suffix to Catalogue No.		
/M25	M25 Cable Entries	
/N	Narrow Beam Distribution (≈5% reduction in output)	
/AS	Asymmetric Distribution (≈11% reduction in output)	
/DM	DALI Dimmable driver	
/RG05	Remote Gearbox complete with 5m Cable to LED Enclosure (0, 10 & 15m cable lengths also available**)	
/4K	4000K (Neutral White) LEDs	
/3K	3000K (Warm White) LEDs	

**Cable construction to BS 6883. For alternative cable length, replace 05 with the required dimension, e.g. /RG10 or /RG00 if the cable will be supplied & fitted by installer.

Accessories order separately

ire Guard	SEVX4-0002
	Order Code

PENDANT MOUNT









