

H-Frame Crossarm Yoke

By Chance Lineman Tools & Equipment
Catalog # [C4000219](#)



The H-Frame Crossarm Yoke is similar to the Tower Yoke in design and application. The two clamp bolts which secure the yoke to the double plank crossarms may be adjusted to three center-to-center positions (9", 11" and 13") to fit various arm sizes- vertical take-up on the crossarm is from 9" to 12". The swiveling trunnion brackets are located 26" center-to-center.

Features

- Snatch blocks hooked into butt ring to keep heandlines from dragging over tower structure, giving clearance to tools in transit
- Bronze mounting hooks are secured with bronze wing nuts on plated steel bolts
- Hook adjustment will fit tower angle from 1-3/4" x 1-3/4" up to 6" x 6"

General

EU RoHS Indicator	No
Max Load Lbs.	12000 lb
Style	Structure Yoke
UPC	096359016441
Working Load Limit	12,000 lb
Working Load Limit Metric	5,443 kg

Dimensions

Dimensions	34 in x 16 in x 8 in
Dimensions Metric	86.4 mm x 40.6 mm x 20.3 mm
Height	8 in
Height Metric	20.3 mm
Length	34 in
Length Metric	86.4 mm
Weight	31 lb
WeightMetric	14 kg
Width	16 in
WidthMetric	40.6 mm

Product Assets

[Literature - Transmission Project Tools and Equipment Checklist](#)