



Insulated Hydraulic Cable Cutter For #6 Solid Copper To 954 kcmil ACSR, 8 ft

By Chance Lineman Tools & Equipment
Catalog # [C4032862](#)

HYDRAULIC WIRE CUTTER - 8FT - 954 ACSR G, A single lineworker can easily cut large-gauge conductors with the power-assist of this tool's closed hydraulic system. It operates like a hydraulic jack, by simply pumping the handle. Epoxiglas™ pole, handle and hydraulic hose have been tested to 100kV per foot. Hydraulic oil has dielectric strength of more than 25kV per ASTM D877. Hose has minimum burst strength of 12,000 psi. Pump provides 9,000 psi maximum pressure. Maintenance and operating instructions are included with each tool.



*Representative Image

Features

- Tested per OSHA & ASTM F711
- Easy operation, powerful construction
- Single lineworker can easily cut large-gauge conductors with the power-assist of this tool's closed hydraulic system
- Operates like a hydraulic jack by simply pumping the handle
- Epoxiglas™ pole, handle and hydraulic hose have been tested to 100kV per foot (ASTM F711)
- Hydraulic oil has dielectric strength of more than 25kV per ASTM D877
- Hose has minimum burst strength of 12,000 psi
- Pump provides 9,000 psi maximum pressure
- Maintenance and operating instructions are included with each tool

General

EU RoHS Indicator	No
Storage Bag Included?	T306-0008 (Bag not included. Must be ordered separately.)
UPC	096359020257

Dimensions

Dimensions	104 in x 1.25 in x 5.61 in
Height	5.61 in
Length	104 in
Length - Live Part Bottom	18.0 in
Weight	23.52 lb
WeightMetric	10.6 kg
Width	1.25 in

Conductor Related

Conductor Size 556 MCM ACSR / 750 kcmil Cu.

Product Assets

[Installation Manuals - CHANCE® Tools Manuals](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CLTE-C4032862-SPEC-EN | REV 6/2024