

## Duckbill Ground Clamp, Type I-Class B-Grade 5H, 1.293" Jaw Opening

By Chance Lineman Tools & Equipment  
Catalog # [C6000197](#)



Duckbill Ground Clamp, Type I-Class B-Grade 5H, 1.293" Jaw Opening

### Features

- Duckbill Ground Clamp
- Continuous Current 400A
- Fault Current 47kA for 15 cycles X/R=30
- Main Line Range Max. 700kcmil CU or 1113kcmil ACSR (1.293")
- Main Line Range Min. #6 Sol. CU (0.162")
- Jumper Range Max. 4/0 Grd. Cable
- Jumper Range Min. #2 Grd. Cable
- ASTM Type I, Class B, Grade 5H
- IEC Rating 35kA (15 cycles)
- Jaws Serrated
- Ferrule Threaded

### General

Eye Screw/T-Handle	250 in-lb
Installation Torque (in-lb)	
Ferrule Installation Torque (in-lb)	250 in-lb
Handle Type	Eyescrew
Jaw Type	Serrated Jaws
Material	Aluminum
Terminal Connection Type	5/8"-11 Thread
Thread Size	5/8-11 UNC
UPC	096359023326

### Dimensions

Jaw Opening Size - Maximum	1.293 in
Jaw Opening Size - Minimum	.162 in
Weight	1.862 lb

### Electrical Ratings

Current Rating	400 A
Fault Current - 15 Cycles	43000 A
Fault Current - 30 Cycles	30000 A
Grounding Wire Capacity Maximum	4/0 Cable w/ Threaded Terminal
Grounding Wire Capacity Minimum	#2 Cable w/ Threaded Terminal

### Certifications And Compliance

Fault Current - ASTM Grade	5H
----------------------------	----

### Logistics

Pallet Quantity	600
-----------------	-----

### Product Assets

[Catalogs - Grounding Equipment](#)  
[Literature - ASTM H-Rated Grounding Sets, Clamps, and Ball Studs](#)  
[Sales Drawings - SA\\_600-0197](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
CLTE-C6000197-SPEC-EN | REV 6/2024