

Duckbill Ground Clamp, Type I- Class A-Grade 5 & 3H, 1.162 in Jaw Opening

By Chance Lineman Tools & Equipment
Catalog # [C6001734](#)



Duckbill Ground Clamp, Type I-Class A-Grade 5 & 3H, 1.162" Jaw
Opening

Features

- Duckbill Ground Clamp
- Continuous Current 400A
- Fault Current Grade 3H - 31kA 15 cycles X/R=30 or Grade 5 - 43kA for 15 cycles or 30kA for 30 cycles
- Main Line Range Max. 566kcmil CU or 900kcmil ACSR (1.162"),
- Main Line Range Min. #6 Sol. CU (0.162")
- Jumper Range Max. 4/0 Grd. Cable
- Jumper Range Min. #2 Grd. Cable
- ASTM Type I, Class A, Grade 3H or Grade 5
- IEC Rating 35kA (15 cycles)
- Jaws Smooth
- Ferrule Threaded

General

Catalog Number	C6001734
Eye Screw/T-Handle	250 in-lb
Installation Torque (in-lb)	
Ferrule Installation Torque (in-lb)	250 in-lb
Handle Type	Eyescrew
Jaw Type	Smooth Jaws
Material	Aluminum
Terminal Connection Type	5/8"-11 Thread
Thread Size	5/8-11 UNC
UPC	096359023876

Dimensions

Dimensions	3.81 in x 6.3 in x 2.23 in
Height	2.23 in
Jaw Opening Size - Maximum	1.162 in
Jaw Opening Size - Minimum	.162 in
Length	3.81 in
Weight	1.372 lb
Width	6.3 in

Electrical Ratings

Current Rating	400 A
Fault Current - 15 Cycles	43000 A
Fault Current - 30 Cycles	30000 A
Grounding Wire Capacity Maximum	4/0 Cable w/ Threaded Terminal
Grounding Wire Capacity Minimum	#2 Cable w/ Threaded Terminal

Certifications And Compliance

Fault Current - ASTM Grade	ASTM Grade 5
----------------------------	--------------

Logistics

Pallet Quantity	750
-----------------	-----

Product Assets

- [Catalogs - Grounding Equipment](#)
- [Sales Drawings - Grounding Clamp \(SA6001734\)](#)
- [Specifications - C6001734](#)