

34.5kV Insulated Bypass Jumper 14 ft (4.2 m)

By Chance Lineman Tools & Equipment
Catalog # [C6010036](#)

BY-PASS JUMPER-34.5kV-8 ft POLE-14 ft OAL, 34.5kV rating between the rubber guards. A solid aluminum rod is epoxi-sealed inside a polypropylene tube which is silicone-sealed inside a 1.5 in Hotstick handle. Brass couplings are threaded onto the end of the solid rod, pinned and three feet of 4/0, clear-jacketed grounding cable is threaded into the coupling. Current capacity is 400 amps.

Features

- 34.5kV By-Pass Jumper (20kV Phase-to-Ground)
- 8 ft Epoxiglas
- 14 ft overall length with threaded terminals
- 3 ft 4/0 clear grounding cable on each end

General

Catalog Number	C6010036
EU RoHS Indicator	No
Thread Size	5/8" - 11 UNC
UPC	096359024491

Dimensions



Diameter	1.5 in
Length	14 ft
Weight	17.6 lb
WeightMetric	7.9 kg

Electrical Ratings

Amperage Rating	400
Current Rating	400 A
Voltage - Maximum	34.5 kV
Voltage Rating	34.5 kV

Product Assets

[Sales Drawings - SA_601-0036](#)
[Specifications - C6010036](#)