

Conductor End Yoke Assembly for Two-Pole Strain Carriers

By Chance Lineman Tools & Equipment
Catalog # [C4011720](#)



Two-pole yokes can be ordered separately to make up any of the two pole strain carriers. The yokes are fabricated of high strength (.75" and 1" thick) aluminum plate. The yokes have 26" width between the center of the adjustable strain poles used with them. Maximum load ratings are 15,000 pounds per insulator string.

Features

- Can be ordered separately to make two pole strain carriers
- Yokes are fabricated of high strength (3/4"- and 1"-thick) aluminum plate
- Yokes have 26" width between center of adjustable strain poles used with them
- Maximum load ratings are 15,000 lbs. per insulator string

General

EU RoHS Indicator	No
Style	Two Pole Strain Carrier - Accessories
UPC	096359017639

Dimensions

Dimensions	30 in x 7.62 in x 6.25 in
Dimensions Metric	76.2 mm x 19.4 mm x 15.9 mm
Height	6.25 in
Height Metric	15.9 mm
Length	30 in
Length Metric	76.2 mm
Weight	40 lb
WeightMetric	18.1 kg
Width	7.62 in
WidthMetric	19.4 mm

Logistics

Pallet Quantity	10
-----------------	----

Product Assets

[Literature - Transmission Project Tools and Equipment Checklist](#)

