

Bus Bar Ground Clamp, Type I-Class A-Grade 5, 4.5" Jaw Opening

By Chance Lineman Tools & Equipment
Catalog # [G3369](#)

Bus Bar Ground Clamp, Type I-Class A-Grade 5, 4.5" Jaw Opening



Features

- Bus-Bar Ground Clamp
- Continuous Current 400A
- Fault Current 43kA for 15 cycles or 30kA for 30 cycles
- Main Line Range Max. 4" x 4" square, 4.5" O.D. Bus
- Main Line Range Min. 4/0 Str. CU (0.500")
- Jumper Range Max. 4/0 Grd. Cable
- Jumper Range Min. #2 Grd. Cable
- ASTM Type I, Class A, Grade 5
- Jaws Smooth
- Ferrule Plain-Plug

General

Eye Screw/T-Handle	300 in-lb
Installation Torque (in-lb)	
Ferrule Installation Torque (in-lb)	N/A
Handle Type	Eyescrew
Jaw Type	Smooth Jaws
Material	Aluminum
Terminal Connection Type	Pressure
Torque Rating	
UPC	096359038191

Dimensions

Jaw Opening Size - Maximum	4.5 in
Jaw Opening Size - Minimum	.368 in
Weight	5.145 lb

Electrical Ratings

Current Rating	400 A
Fault Current - 15 Cycles	43000 A
Fault Current - 30 Cycles	30000 A
Grounding Wire Capacity Maximum	4/0 Cable w/ Plain Terminal
Grounding Wire Capacity Minimum	#2 Cable w/ Plain Terminal

Certifications And Compliance

Fault Current - ASTM Grade ASTM Grade 5

Logistics

Carton Quantity	3
Pallet Quantity	90

Product Assets

[Catalogs - Grounding Equipment](#)
[Sales Drawings - SA_G3369](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CLTE-G3369-SPEC-EN | REV 6/2024