

Insulated Platform, 8 ft

By Chance Lineman Tools & Equipment
Catalog # [C4021079](#)

Unique design features 12 in (.305 m) of insulating 2 in (51 mm) diameter Epoxiglas poles connecting the platform to the mounting bracket. Secures to pole via chain binders from included Fixed Mount.

Features

- Optional Epoxiglas Tripod, Rail, and Pivot Base sold separately
- IMPORTANT: Rails and Tripods are not suited for use as a fall restraint device
- 8 ft (2.44m) overall length, platform board is 77 in (1.96 m)
- 500 lb. (226.8 kg) Maximum Load Rating
- Insulating members manufactured to same standards as Chance Hotsticks: OSHA subpart V, section 1926.951(d), IEC 60855, and ASTM 711
- Three strips of 2 in (51 mm) wide non-skid tape extend the length of the platform surface

General

Catalog Number	C4021079
Strength Rating - Ultimate	500 lb
Style	Insulated Platform
UPC	096359243847

Dimensions

Dimensions	96 in x 12.13 in x 6.19 in
------------	----------------------------



Dimensions Metric	243.8 mm x 30.8 mm x 15.7 mm
Height	6.19 in
Height Metric	15.7 mm
Length	96 in
Length Metric	243.8 mm
Weight	76 lb
WeightMetric	34.4 kg
Width	12.13 in
WidthMetric	30.8 mm

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Product Assets

- [Catalogs - Ladders & Platforms](#)
- [Installation Manuals - Instructions for CHANCE® Temporary Work Platform](#)
- [Installation Manuals - CHANCE® Epoxiglas™ Live-Line Tool Instruction Manual](#)
- [Specifications - C4021079](#)
- [Video - CHANCE Installation and Safety guide for Platforms](#)