

Epoxiglas Heavy Duty Swivel Hook Ladder W/8" Hooks, 8'

By Chance Lineman Tools & Equipment
Catalog # [H49058](#)


LADDER, 2.5X8' W/8" HOOKS, Epoxiglas Hook Ladders have many applications in high voltage maintenance to position linemen in the most advantageous working location, making line repairs possible at otherwise almost inaccessible places. All hooks are formed from 1"-diameter tempered steel and can be swiveled to best fit various angles on the structure. Steel chains clip to the hooks to assist in securing the ladder to a support. Rung material for both rated ladders are 1.25" Epoxiglas, sand coated.

Features

- Meets ASTM F711 and IEC 61478 - Category 2
- Designed to effectively position linemen for high-voltage maintenance
- Make line repairs possible, even in inaccessible places
- Two basic styles of Epoxiglas Hook Ladders are available - Regular Duty Ladders with 2" siderails for vertical suspension applications and Heavy Duty Ladders with 2-1/2" siderails for tagged-out positions
- Hooks are formed from 1"-diameter tempered steel
- These hooks can be swiveled to best fit various angles on structure
- Ladders include 8"-dia. hooks
- 14"- or 18"-dia. hooks can be ordered for other structure applications
- Steel chains clip to hooks to assist in securing ladder to support
- Rung material for both rated ladders are 1-1/4" sand-coated Epoxiglas

General

Catalog Number	H49058
EU RoHS Indicator	No
Strength Rating - Ultimate	1250 lb



*Representative Image

Style	Swivel Hook Ladder
UPC	096359041290

Dimensions

Diameter	2.5 in
Diameter - Hook	8 in
Dimensions	8 ft x 27 in x 252 in
Dimensions Metric	2.4 m x 68.6 mm x 640.1 mm
Height	252 in
Height Metric	640.1 mm
Length	8 ft
Length Metric	2.4 m
Side Rail Space	15 in, 38 cm
Weight	150 lb
WeightMetric	68 kg
Width	27 in
WidthMetric	68.6 mm

Product Assets

[Installation Manuals - CHANCE® Tools Manuals](#)
[Literature - Transmission Project Tools and Equipment Checklist](#)
[Literature - High Voltage Insulated Ladders](#)
[Sales Drawings - SA_H4905](#)
[Specifications - H49058](#)