



# 15kV Rubber Glove Jumper Set 12 ft (3.6 m) 2/0 with Orange Clamps

By Chance Lineman Tools & Equipment  
Catalog # [C6010164](#)



15kV 12 ft 2/0 Rubber Glove Jumper Set, 15kV Orange Clamps

## Features

- Designed and tested to ASTM F2321
- Complete set rated to 15kV
- Includes G4758 15kV Rubber Glove Jumper Clamps and 12ft of S10045 2/0 15kV Jumper Cable
- Continuous current rating of 300 amps
- Conductor range of #6 CU to 795 ACSR
- Used for bypassing work areas when equipment is under repair, upgrading lines, and making temporary or emergency repairs
- Clamps have 5-5/8" below the handguard
- Adequate rubber gloves must be worn when installing or removing jumper clamps

## General

Catalog Number	C6010164
EU RoHS Indicator	No
Style	Rubber Glove Applied
UPC	096359024583

## Dimensions

Length	12 ft
Length - Jumper	144 in
Weight	16.6 lb

WeightMetric	7.5 kg
--------------	--------

## Electrical Ratings

Amperage Rating	300
Current Rating	300 A
Voltage - Maximum	15 kV
Voltage Rating	15 kV

## Conductor Related

Conductor Diameter (Main) - Maximum	0.7 in
Conductor Diameter (Main) - Minimum	0.1 in
Conductor Size	2/0 AWG

## Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

## Logistics

Pallet Quantity	24
-----------------	----

## Product Assets

[Catalogs - Jumpers & Load Pickup Tools](#)  
[Specifications - C6010164](#)



A Hubbell brand