

Adjustable Ladder Hook, 14"

By Chance Lineman Tools & Equipment
Catalog # [H49251](#)

HOOK, 14" ASSEMBLY, The Adjustable Hook is easily attached in one quick operation. Just position on the Epoxiglas side rail, swing the bolt around and tighten the wing nut. The hook is made of 1" diameter heat-treated, rust-resistant steel and is equipped with a rugged chain and chain snap for a positive lock between the ladder and the support. Hooks are rated at 1,000 lb. per pair. Adjustable Hooks for Epoxiglas ladders are popular with hot line maintenance and construction crews. Adjustable hooks can be used with Epoxiglas Hook Ladders to obtain a more convenient position, or attached to an Epoxiglas Service Ladder for use as a temporary hook ladder. Adjustable Hooks are ideal for suspension use where there are uneven or sloping supports.



*Representative Image

Features

- Easily attaches in one quick operation
- Position on Epoxiglas™ side rail, swing bolt around and tighten wing nut
- Made of 1"-dia. heat-treated, rust-resistant steel
- Equipped with rugged chain and chain snap for positive lock between ladder and support
- Hooks are rated at 1,000 lbs. per pair
- Adjustable hooks can be used with Epoxiglas Hook Ladders to obtain a more convenient position
- Can be attached to an Epoxiglas Service Ladder for use as a temporary hook ladder
- Adjustable Hooks are ideal for suspension use for uneven or sloping supports

General

EU RoHS Indicator	No
Strength Rating - Ultimate	1000 lb
Style	Adjustable Ladder Hook
U-Rail Size	2.5 in, 6.5 cm
UPC	096359041320

Dimensions

Diameter	2.5 in
Diameter - Hook	14 in
Dimensions	18.5 in x 13 in x 8.5 in
Dimensions Metric	47.0 mm x 33.0 mm x 21.6 mm
Height	8.5 in
Height Metric	21.6 mm
Length	18.5 in
Length Metric	47 mm
Weight	16 lb
WeightMetric	7.2 kg
Width	13 in
WidthMetric	33 mm

Logistics

Pallet Quantity	16
-----------------	----

Product Assets

[Installation Manuals - CHANCE® Tools Manuals](#)
[Literature - Transmission Project Tools and Equipment Checklist](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CLTE-H49251-SPEC-EN | REV 6/2024