



# 15kV By-Pass Jumper - 16 ft, 2/0 Cable

By Chance Lineman Tools & Equipment  
Catalog # C6010262



INSULATED BY-PASS JUMPER - 15kV-2/0-16 ft, A total of 16 ft, the tool features mid-span an orange 8 ft epoxy-resin, rigid 1.5 in fiberglass-reinforced-plastic (FRP) tube that serves as a support for easy handling of the jumper set by rubber gloves or hotline tools. Two non-metallic hangers-one at each end of the FRP support tube-provide for parking the by-pass clamps while moving the jumper set into or out of the work area. 4 ft of 1/0 cable extends from both ends of the rigid support.

## Features

- INSULATED BY-PASS JUMPER - 15kV-2/0-16 ft
- A total of 16 ft, the tool features mid-span an orange 8 ft epoxy-resin, rigid 1.5 in fiberglass-reinforced-plastic (FRP) tube that serves as a support for easy handling of the jumper set by rubber gloves or hotline tools
- Two non-metallic hangers-one at each end of the FRP support tube-provide for parking the by-pass clamps while moving the jumper set into or out of the work area
- 4 ft of 1/0 cable extends from both ends of the rigid support

## General

EU RoHS Indicator	No
Torque Rating	250 in-lbs
UPC	096359024804

## Dimensions

Diameter	1.5 in
Jaw Opening Size - Maximum	1.5 in
Jaw Opening Size - Minimum	.162 in
Length	16 ft
Length - Jumper	192 in
Weight	21.5 lb
WeightMetric	9.7 kg

## Electrical Ratings

Amperage Rating	300
Current Rating	300 A
Voltage - Maximum	15 kV
Voltage Rating	15 kV

## Conductor Related

Conductor Diameter (Main) - Maximum	1.5 in
Conductor Diameter (Main) - Minimum	0.162 in
Conductor Size	2/0 AWG

## Product Assets



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CLTE-C6010262-SPEC-EN | REV 1/2024