


## Tower Handline Gin

By Chance Lineman Tools & Equipment  
Catalog # [M1979](#)

The aluminum angle Tower Handline Gin is 3' x 3" x .25" with an aluminum-weld end-plate securing a bronze, free-swivel butt ring. Snatch blocks hooked into the butt ring keep handlines from dragging over the tower structure, giving clearance to tools in transit. Bronze mounting hooks of the Tower Gin are held in place with bronze wing nuts on plated steel bolts. Hook adjustment will fit tower angle from 1.75" x 1.75" up to 6" x 6". Maximum load for the gin is 500 pounds.



### Features

- Snatch blocks hooked into butt ring to keep handlines from dragging over tower structure, giving clearance to tools in transit
- Bronze mounting hooks are secured with bronze wing nuts on plated steel bolts
- Hook adjustment will fit tower angle from 1-3/4" x 1-3/4" up to 6" x 6"
- Maximum load for the gin is 500 lbs.

### General

EU RoHS Indicator	No
Style	Tower Gin
UPC	096359044154

### Dimensions

Dimensions	21.0 in x 10 in x 3 in
Dimensions Metric	533.4 mm x 25.4 mm x 7.6 mm
Height	3 in
Height Metric	7.6 mm
Length	21 in
Length Metric	533.4 mm
Lengths - Extended	21
Weight	7 lb
WeightMetric	3.1 kg
Width	10 in
WidthMetric	25.4 mm

### Product Assets

[Literature - Transmission Project Tools and Equipment Checklist](#)