



# 3/4 & 1-1/2 Ton Convertible Regular Handle Nylon-Strap Hoist

By Chance Lineman Tools & Equipment  
Catalog # PSC3090451

Every Chain Hoist is proof-tested and factory-operated at 150% of capacity rating



## Features

- Adapts to varying field needs
- Adds 3 ft of lift distance when rigged at the lower rating
- To rig hoist for higher rating, keep load-hook sheave mounted midway on strap when it is becketed (doubled, with the end of strap secured to hoist frame)
- To convert to lower rating, secure the load hook sheave through loop in free end of strap

## General

EU RoHS Indicator	No
Style	Convertible Strap Hoist
UPC	096359395690
Working Load Limit	3,000 lb
Working Load Limit Metric	1,360 kg

## Dimensions

Dimensions	30 in x 8.38 in x 5 in
Height	5 in
Length	30 in
Length Metric	76.2 mm
Weight	13.5 lb
WeightMetric	6.1 kg
Width	8.38 in

## Logistics

Standard Package	1
------------------	---

## Product Assets

[Catalogs - Mechanical Hoists \(1100\)](#)  
[Installation Manuals - CHANCE 3/4-1.5 & 1-2-Ton Convertible Rated Nylon Strap Hoist Operating and Servicing Instructions \(P309-0558\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CLTE-PSC3090451-SPEC-EN | REV 1/2024