


## Duckbill Ground Clamp, Type I-Class A-Grade 3, 0.574" Jaw Opening

By Chance Lineman Tools & Equipment  
Catalog # [G18102](#)



Duckbill Ground Clamp, Type I-Class A-Grade 3, 0.574" Jaw Opening

### Features

- Duckbill Ground Clamp
- Continuous Current 300A
- Fault Current 27kA for 15 cycles or 20kA for 30 cycles
- Main Line Range Max. 250kcmil str. CU or 4/0 ACSR (0.574")
- Main Line Range Min. #6 Sol. CU (0.162")
- Jumper Range Max. 2/0 Grd. Cable
- Jumper Range Min. #2 Grd. Cable
- ASTM Type I, Class A, Grade 3
- Jaws Smooth
- Ferrule Plain-Plug

### General

Eye Screw/T-Handle	250 in-lb
Installation Torque (in-lb)	
Ferrule Installation Torque (in-lb)	250 in-lb
Handle Type	Eyescrew
Jaw Type	Smooth Jaws
Material	Aluminum
Terminal Connection Type	Pressure
UPC	096359038122

### Dimensions

Jaw Opening Size - Maximum	.574 in
Jaw Opening Size - Minimum	.162 in
Weight	1.264 lb

### Electrical Ratings

Current Rating	300 A
Fault Current - 15 Cycles	27000 A
Fault Current - 30 Cycles	20000 A
Grounding Wire Capacity Maximum	2/0 Cable w/ Plain Terminal
Grounding Wire Capacity Minimum	#2 Cable w/ Plain Terminal

### Certifications And Compliance

Fault Current - ASTM Grade      ASTM Grade 3

### Logistics

Pallet Quantity      1600

### Product Assets

[Catalogs - Grounding Equipment](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
CLTE-G18102-SPEC-EN | REV 6/2024