



3/4 & 1-1/2 Ton Convertible All Hotstick Style Nylon-Strap Hoist

By Chance Lineman Tools & Equipment
Catalog # [PSC3090663](#)

Every Chain Hoist is proof-tested and factory-operated at 150% of capacity rating



Features

- Adapts to varying field needs
- Adds 3 ft of lift distance when rigged at the lower rating
- To rig hoist for higher rating, keep load-hook sheave mounted midway on strap when it is becketed (doubled, with the end of strap secured to hoist frame)
- To convert to lower rating, secure the load hook sheave through loop in free end of strap

General

UPC	096359565567
Working Load Limit	3,000 lb
Working Load Limit Metric	1,360 kg

Dimensions

Length	30 in
Length Metric	76.2 mm
Weight	14.65 lb
WeightMetric	6.6 kg

Logistics

Standard Package	1
------------------	---

Product Assets

[Catalogs - Mechanical Hoists \(1100\)](#)
[Installation Manuals - CHANCE 3/4-1.5 & 1-2-Ton Convertible Rated Nylon Strap Hoist Operating and Servicing Instructions \(P309-0558\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CLTE-PSC3090663-SPEC-EN | REV 1/2024