



## 2 Ton Regular Handle Nylon-Strap Ratchet Hoist

By Chance Lineman Tools & Equipment  
Catalog # [PSC3120000](#)

Every Chain Hoist is proof-tested and factory-operated at 150% of capacity rating



### Features

- Always use with insulated link sticks of appropriate length
- Plastisol cap on handle end for rubber glove work
- Hotstick rings on hooks and latches
- 2-Ton units employ a sheave-mounted hook in a double-strap becket
- 3'9" Standard lift distance
- 27" minimum between hooks

### General

EU RoHS Indicator	No
Strength Rating - Ultimate	4000 lb
Style	Regular Handle
UPC	096359395683
Working Load Limit	4,000 lb
Working Load Limit Metric	1,814 kg

### Dimensions

Dimensions	22 in x 8.38 in x 5 in
Dimensions Metric	55.9 mm x 21.3 mm x 12.7 mm
Height	5 in
Height Metric	12.7 mm
Length	22 in
Length Metric	55.9 mm
Weight	20 lb
WeightMetric	9.3 kg
Width	8.38 in
WidthMetric	21.3 mm

### Logistics

Pallet Quantity	20
Standard Package	1

### Product Assets

[Catalogs - Load Handling Accessories](#)  
[Installation Manuals - Strap Hoist Instruction Manual](#)



A Hubbell brand