



# Digital Phasing Meter Kit for 40 to 240kV

By Chance Lineman Tools & Equipment  
Catalog # [PSC4033466](#)

Large, backlit, direct-reading display easily determines phase relationships and approximate voltage, line-to-line or line-to-ground on transmission circuits



## Features

- Kit Includes: (1) Instruction Manual, (1) PSC4033455 Tester (102" Long), (2) C4030459 Handles (96" Long), (1) P6218 Handle Bag, (1) C4030464 Bag for Tester
- Large Digital Display with Backlight and Hold modes
- Two high-impedance components in fiberglass poles, each threaded for interchangeable probes
- 22-foot-long insulated flexible cable from voltmeter stores on reel on other pole
- Must be used with 2 Epoxiglas Insulating Universal Hotsticks of appropriate length (included in kit)

## General

EU RoHS Indicator No  
UPC 096359503538

## Dimensions

Weight 60 lb  
WeightMetric 27.2 kg

## Logistics

Standard Package 1

## Product Assets

[Installation Manuals - CHANCE Digital Transmission Phasing Testers Operating Instructions](#)