

Epoxiglas Tree Trimmer - 1.25 in - 18 in with Universal Adapter

By Chance Lineman Tools & Equipment

Catalog # [H21064](#)



TREE TRIMMER - 1.25" X 18" W/ UNIVERSAL, Tree Trimmers are designed to cut up to 1.5" dia. branches and are especially useful around energized conductors or in hard to get places. The Tree Trimmer head features sharpened stationary and movable blades made of dropforged steel. The rope and pulley arrangement gives the operator a mechanical advantage of 3 to 1. For example, a 10-lb. pull on the rope will exert a 30-lb. force on the cutter head lever. Ball bearing pulleys are employed for free operation. The rope furnished with each Universal Tool Fitting is provided with 25' of rope.

Features

- Designed to cut up to 1½" diameter branches
- Useful around energized conductors or in hard-to-reach places
- Head features sharpened stationary and movable blades made of dropforged steel
- Rope and pulley arrangement gives operator a mechanical advantage of 3 to 1
- Example: A 10-lb. pull on rope will exert a 30-lb. force on the cutter head lever
- Ball bearing pulleys are employed for free operation
- Rope furnished with each tree trimmer is 25' long
- Accommodates a 6' extension on the basic tool
- The 18" long Universal Tool Fitting is provided with 25' of rope
- A Universal Pruning Saw can be added to the universal fitting on the side of the head mount
- Spliced extensions fasten securely to the tool with leaf spring button loc

General

Catalog Number H21064

EU RoHS Indicator Style	No Epoxiglas Tree Trimmer w/ Universal Fitting
Type UPC	Cutters 096359039778

Dimensions

Length	36 in
Weight	6.9 lb
WeightMetric	3.1 kg

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Product Assets

- [Catalogs - Cutters](#)
- [Installation Manuals - CHANCE® Epoxiglas™ Live-Line Tool](#)
- [Instruction Manual](#)
- [Sales Drawings - SA_H2106-4](#)
- [Specifications - H21064](#)