

15kV Temporary Cutout

By Chance Lineman Tools & Equipment
Catalog # [PSC6010341](#)

CUTOUT,TEMPORARY 15KV POLYMER, To provide fuse protection during live-line maintenance, the temporary cutout tool simply clamps onto primary conductor with a Grip-All clampstick. Brass stud at lower end accepts clamp on temporary tap jumper. Insulated bushing and hot parts are from Type C-Polymer cutouts: Upper contact with integral sleet shield and hooks for operation by loadbreak tool and lower trunnion of cast bronze. Fusetube must be fitted with fuselink rated no larger than 100 amps.

Features

- To provide fuse protection during live-line maintenance, temporary cutout tool simply clamps onto primary conductor with a Grip-All clampstick
- Brass stud at lower end accepts clamp on temporary tap jumper
- Insulated bushing and hot parts are from Chance Type C-Polymer cutouts
- Upper contact with integral sleet shield and hooks for operation by loadbreak tool and lower trunnion of cast bronze
- Fusetube must be fitted with fuselink rated no larger than 100 amps
- Available in ratings for 15kV and 27kV systems
- Tools come with or without a pivot-lever closing device
- 250 in.-lb. torque for clamp eyescrew
- Includes tap stud with 1/2" diameter

General

EU RoHS Indicator	No
Maximum interrupting capacity	10,000 Amps
Style	100 Amp Fuse Tube
UPC	096359391517

Dimensions

Weight	12 lb
WeightMetric	5.4 kg

Electrical Ratings

Amperage Rating	100
Voltage - Maximum	15 kV
Voltage Rating	15000 V



Conductor Related

Conductor Diameter (Main) - Maximum	1.16 in
-------------------------------------	---------

Logistics

Pallet Quantity	32
-----------------	----

Product Assets

[Sales Drawings - Temporary Cutout \(SA6010341\)](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CLTE-PSC6010341-SPEC-EN | REV 6/2024