

Temporary Cutout 27kV Pivot Lever Style

By Chance Lineman Tools & Equipment
Catalog # [PSC6010346](#)

CUTOUT,TEMPORARY 27kV POLY LINEBREAK, To provide fuse protection during live-line maintenance, the temporary cutout tool simply clamps onto primary conductor with a Grip-All clampstick. Brass stud at lower end accepts clamp on temporary tap jumper. Insulated bushing and hot parts are from Type C-Polymer cutouts: Upper contact with integral sleet shield and hooks for operation by loadbreak tool and lower trunnion of cast bronze. Fusetube must be fitted with fuselink rated no larger than 100 amps.

Features

- To provide fuse protection during live-line maintenance, temporary cutout tool simply clamps onto primary conductor with a Grip-All clampstick
- Brass stud at lower end accepts clamp on temporary tap jumper
- Insulated bushing and hot parts are from Chance Type C-Polymer cutouts
- Upper contact with integral sleet shield and hooks for operation by loadbreak tool and lower trunnion of cast bronze
- Fusetube must be fitted with fuselink rated no larger than 100 amps
- Available in ratings for 15kV and 27kV systems
- Tools come with or without a pivot-lever closing device
- 250 in.-lb. torque for clamp eyescrew

General

EU RoHS Indicator	No
Style	100 Amp Fuse Tube w/ Pivot Lever
UPC	096359397014

Dimensions

Weight	12.5 lb
WeightMetric	5.6 kg

Electrical Ratings

Amperage Rating	100
Voltage - Maximum	27 kV
Voltage Rating	27000 V



Conductor Related

Conductor Diameter (Main) - 1.16 in
Maximum

Product Assets

[Sales Drawings - SA_6010341](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CLTE-PSC6010346-SPEC-EN | REV 6/2024