

Epoxiglas Spliced Ladder, 2.5 in X 10 ft Middle Section

By Chance Lineman Tools & Equipment
Catalog # [T4020423](#)

LADDER, CENTER 10 FT, Epoxiglas Spliced Ladders are available in combinations of up to 32 feet in 2.5" diameter side rails, all splices are interchangeable, thus offering a variety of total reach with a few ladder sections in more convenient transportation lengths. One-inch diameter steel rods, 8" in diameter, are arched to hook over structural shapes are furnished on all top section units. The hooks are complete with steel chains- larger hooks are available on special order. Heavy-duty Epoxiglas Ladders, manufactured in short, easy-to-transport lengths, are joined with the Rigid Ladder Splice to form an unshakable, rigid splice- two eye pins in each rail, with a klik pin in the end of each are supplied.

Features

- Meets ASTM F711 and IEC 61478 - Category 2
- Available in combinations of up to 32' in 2-1/2"-dia. side rails
- All splices are interchangeable, offering a variety of total reach
- Available in various section lengths for convenient transport
- Hooks are made of 1" diameter steel and have an 8" diameter arch to hook over structural shapes
- Hooks are complete with steel chains
- Larger hooks are available on special order
- Heavy-duty Chance Epoxiglas Ladders, manufactured in short, easy-to-transport lengths, are joined with Chance Rigid Ladder Splice to form unshakable, rigid splice
- Two eye pins with a klik pin in the end of each are supplied with each splice

General

EU RoHS Indicator	No
Style	Spliced Ladder
UPC	096359059066



Dimensions

Dimensions	120.0 in x 27 in x 252 in
Dimensions Metric	304.8 cm x 68.6 mm x 640.1 mm
Height	252 in
Height Metric	640.1 mm
Length	120 in
Length Metric	304.8 cm
Weight	174 lb
WeightMetric	78.9 kg
Width	27 in
WidthMetric	68.6 mm

Product Assets

[Installation Manuals - CHANCE® Tools Manuals](#)
[Literature - Transmission Project Tools and Equipment Checklist](#)
[Literature - High Voltage Insulated Ladders](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CLTE-T4020423-SPEC-EN | REV 6/2024