

Extension Arm, 2.5 in X 6 ft

By Chance Lineman Tools & Equipment
Catalog # T4032417



*Representative Image

EXTENSION ARM 2.5IN X 72IN LONG - 2 WH, The Epoxiglas™ Extension Arm is designed for use on voltages up to and including 15 kV where reconductoring or insulator replacement is necessary. The Epoxiglas Extension Arm can be used on voltages up to 34.5 kV providing the wireholders are fitted with M4805-7 insulators. The Extension Arm is suspended under the crossarm by brackets to enable to conductor to be removed from the original crossarm and placed in the wireholder mounted on the Epoxiglas Extension Arm.

Features

Extension Arm installed on crossarm. Unit is shown here equipped with M4805-7 insulators on the wireholders. Order insulators separately.

General

Catalog Number	T4032417
Duty	Standard Duty
EU RoHS Indicator	No
Number of Wireholders	2
Type	Arm
UPC	096359059691
Working Load Limit	150 lb
Working Load Limit Metric	68 kg

Dimensions

Dimensions	10 in x 13 in x 72.5 in
Dimensions Metric	25.4 mm x 33.0 mm x 184.2 mm
Height	72.5 in

Height Metric	184.2 mm
Length	10 in
Length Metric	25.4 mm
Weight	23 lb
WeightMetric	10.4 kg
Width	13 in
WidthMetric	33 mm

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
------------------------	----------------------

Logistics

Pallet Quantity	96
-----------------	----

Product Assets

[Catalogs - Conductor Support Equipment](#)
[Installation Manuals - CHANCE® Tools Manuals](#)
[Sales Drawings - SA_4032417](#)
[Specifications - T4032417](#)