


15kV Hotstick Jumper Set 12 ft (3.6 m) #2 Cable

By Chance Lineman Tools & Equipment
Catalog # [T6010281](#)



15kV, 12 ft of #2 cable, insulated jumper for hotstick applications, main line range of 0.162 in to 1.5 in

Features

- Meets ASTM F2321 Standard Specification
- Two C-type grounding clamps (C6001743) and two threaded copper ferrules
- Main Line Range: #6 solid copper (0.162") through 1590kcmil ACSR (1.50")
- 15kV EPR-insulated jumper cable
- Other clamps and cable combinations available upon request

General

Cable Length	12 ft
Cable Length Metric	3.6 m
EU RoHS Indicator	No
Style	Hotstick Applied
UPC	096359061847

Dimensions

Length	12 ft
Weight	9.8 lb
WeightMetric	4.4 kg

Electrical Ratings

Amperage Rating	200
Current Rating	200 A
Voltage - Maximum	15 kV
Voltage Rating	15 kV

Conductor Related

Conductor Diameter (Main) - Maximum	1.5 in
Conductor Diameter (Main) - Minimum	0.162 in
Conductor Size	#2 AWG

Product Assets



A Hubbell brand