




Jumper Set for Hotstick Applications - 15kV, 15 ft 2/0 Cable

By Chance Lineman Tools & Equipment
Catalog # T6010286



*Representative Image

Features

- Meets ASTM F2321 Standard Specification
- Two C-type grounding clamps (C6001743) and two threaded copper ferrules
- Main Line Range: #6 solid copper (0.162") through 1590kcmil ACSR (1.50")
- 15kV EPR-insulated jumper cable
- Other clamps and cable combinations available upon request

General

Cable Length	15 ft
EU RoHS Indicator	No
Style	Hotstick Applied
UPC	096359061892

Dimensions

Length	15 ft
Weight	5.8 lb
WeightMetric	2.6 kg

Electrical Ratings

Amperage Rating	300
Current Rating	300 A
Voltage - Maximum	15 kV
Voltage Rating	15 kV

Conductor Related

Conductor Diameter (Main) - Maximum	1.5 in
Conductor Diameter (Main) - Minimum	0.162 in
Conductor Size	2/0 AWG

Product Assets



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CLTE-T6010286-SPEC-EN | REV 1/2024