

Steel Tower Yoke

By Chance Lineman Tools & Equipment
Catalog # [H478322](#)



The Tower Yoke fits over the tower arm, serving as a support for the Strain Poles to relieve tension on the suspension insulator string through the “hot end” yoke and the conductor yoke plate. The legs of the yoke are so designed that they can be adjusted to fit most tower structure configurations. Still, it is recommended that the design drawings of the tower arms be submitted to A. B. Company with the Tower Yoke order for engineering evaluation to assure a proper fit. Swivel trunnions are 26” center to center.

Features

- Snatch blocks hooked into butt ring to keep heandlines from dragging over tower structure, giving clearance to tools in transit
- Bronze mounting hooks are secured with bronze wing nuts on plated steel bolts
- Hook adjustment will fit tower angle from 1-3/4” x 1-3/4” up to 6” x 6”
- Maximum load for the gin is 500 lbs.

General

Catalog Number	H478322
Max Load Lbs.	12000 lb
Style	Structure Yoke
UPC	096359040866
Working Load Limit	12,000 lb
Working Load Limit Metric	5,443 kg

Dimensions

Dimensions	27.56 in x 19.38 in x 8.38 in
Dimensions Metric	70.0 mm x 49.2 mm x 21.3 mm
Height	8.38 in
Height Metric	21.3 mm
Length	27.56 in
Length Metric	70 mm
Weight	34 lb
WeightMetric	15.4 kg
Width	19.38 in
WidthMetric	49.2 mm

Logistics

Pallet Quantity	12
-----------------	----

Product Assets

- [Catalogs - Transmission Tools](#)
[Literature - Transmission Project Tools and Equipment Checklist](#)
[Sales Drawings - SA H478322 TOWER YOKE](#)
[Specifications - H478322](#)