



2" Square Shaft Helical Extension (SS200), 14/14 x 7ft

By CHANCE Foundation Solutions
Catalog # [C1100581](#)

SS200, 7' (2134 mm) with 14"/14" helices



*Representative Image

Features

- Finish: Galvanized
- Capacity of helical pile can be determined by measuring installation
- Bolt and nut are assembled to extension at the factory

General

Application	Helical Anchoring
Catalog Number	C1100581
Coating	Galvanized, ASTM A-153
EU RoHS Indicator	No
Number of Helices	2
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	150000 lb.
Torque Rating	16000 ft-lbs
Type	Anchor Extensions
UPC	096359010036

Dimensions

Anchor Helix Diameter(s)	14 in - 14 in
Length	84 in
Weight	148.715 lb

Logistics

Pallet Quantity	12
Standard Package	1

Product Assets

- [Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure](#)
- [Catalogs - CHANCE Civil Product Catalog](#)
- [Installation Manuals - Chance Helical Pile/Anchor Installation Log Form to record installation details of Chance helical piles.](#)
- [Literature - Square Shaft Efficient Helical Pile Design](#)
- [Literature - New Construction Helical Pile Foundation System](#)
- [Sales Drawings - SS200 Anchors](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Video - CHANCE Square Shaft Anchor Tools Selection Process](#)
- [Video - CHANCE Square Shaft Anchor Installation](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CN-C1100581-SPEC-EN | REV 6/2024