

## Epoxiglas Swivel Hook Ladder W/18" Hooks, 12'

By Chance Lineman Tools & Equipment  
Catalog # [H490412B](#)



\*Representative Image

Epoxiglas Hook Ladders have many applications in high voltage maintenance to position linemen in the most advantageous working location, making line repairs possible at otherwise almost inaccessible places. All hooks are formed from 1"-diameter tempered steel and can be swiveled to best fit various angles on the structure. Steel chains clip to the hooks to assist in securing the ladder to a support. Rung material for both rated ladders are 1.25" Epoxiglas, sand coated.

### Features

- Meets ASTM F711 and IEC 61478 - Category 2
- Designed to effectively position linemen for high-voltage maintenance
- Make line repairs possible, even in inaccessible places
- Two basic styles of Epoxiglas Hook Ladders are available - Regular Duty Ladders with 2" siderails for vertical suspension applications and Heavy Duty Ladders with 2-1/2" siderails for tagged-out positions
- Hooks are formed from 1"-diameter tempered steel
- These hooks can be swiveled to best fit various angles on structure
- Ladders include 8"-dia. hooks
- 14"- or 18"-dia. hooks can be ordered for other structure applications
- Steel chains clip to hooks to assist in securing ladder to support
- Rung material for both rated ladders are 1-1/4" sand-coated Epoxiglas

### Dimensions

Diameter	2 in
Diameter - Hook	18 in
Dimensions	159 in x 30 in x 12 in
Dimensions Metric	403.9 mm x 76.2 mm x 30.5 mm
Height	12 in
Height Metric	30.5 mm
Length	159 in
Length Metric	403.9 mm
Side Rail Space	15 in
Weight	250 lb
WeightMetric	113.4 kg
Width	30 in
WidthMetric	76.2 mm

### Product Assets

[Installation Manuals - CHANCE® Tools Manuals](#)  
[Literature - Transmission Project Tools and Equipment Checklist](#)  
[Sales Drawings - SA\\_H4904](#)

### General

Strength Rating - Ultimate	750 lb
Style	Swivel Hook Ladder
UPC	096359700166



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
CLTE-H490412B-SPEC-EN | REV 6/2024