



3.5" Round Shaft Extension(RS3500.300), 7ft

By CHANCE Foundation Solutions
Catalog # [C1500026CU](#)

RS3500.300, 84" long with no helix.



Features

- Finish: Galvanized
- ICC-ES Approved Seismic Categories A-F
- Capacity can be determined by measuring installation torque

Application

Helical Anchoring

General

Coating	Hot Dip Galvanized
Holding Capacity Soil (Kt)	7
Shaft Type	RS
Torque Rating	13000 ft-lbs
Type	Anchor Extensions
UPC	096359704157

Dimensions

Length	83.00 in
Length - Effective	77.00 in
Weight	77.00 lb

Product Assets

- Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure (BR04146E)
- Catalogs - CHANCE Helical Solutions Product Catalog (CA04140E)
- Engineering Drawing - SA1070573CU
- ISO Certificates - Centralia_Operations_ISO_9001_2015
- Literature - New Construction Helical Pile Foundation System (SF04215E_0419)
- Sales Drawings - SA1070573CU
- SDS - MSDS - Galvanized Steel Products
- Video - CHANCE 4.3 Helicap 3.0 Torque Graph (VIO4167E0420)
- Video - CHANCE 4.2 Helicap 3.0 Capacity Graph Tab (VIO4165E0420)
- Video - Hubbell Power Systems Helical Pile Shake Table Testing (VIO4112E)

Related Products

- 450315P
- P1100814P
- 058331P - Single-Coil Spring Lockwasher for 3/4-in bolt



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CN-C1500026CU-SPEC-EN | REV 7/2023