

Epoxiglas Heavy Duty Swivel Hook Ladder W/18" Hooks, 16'

By Chance Lineman Tools & Equipment
Catalog # [H490516B](#)



LADDER, 2.5X16'4" W/ 18" HK, Epoxiglas Hook Ladders have many applications in high voltage maintenance to position linemen in the most advantageous working location, making line repairs possible at otherwise almost inaccessible places. All hooks are formed from 1"-diameter tempered steel and can be swiveled to best fit various angles on the structure. Steel chains clip to the hooks to assist in securing the ladder to a support. Rung material for both rated ladders are 1.25" Epoxiglas, sand coated.

*Representative Image

Features

- Meets ASTM F711 and IEC 61478 - Category 2
- Designed to effectively position linemen for high-voltage maintenance
- Make line repairs possible, even in inaccessible places
- Two basic styles of Epoxiglas Hook Ladders are available - Regular Duty Ladders with 2" siderails for vertical suspension applications and Heavy Duty Ladders with 2-1/2" siderails for tagged-out positions
- Hooks are formed from 1"-diameter tempered steel
- These hooks can be swiveled to best fit various angles on structure
- Ladders include 8"-dia. hooks
- 14"- or 18"-dia. hooks can be ordered for other structure applications
- Steel chains clip to hooks to assist in securing ladder to support
- Rung material for both rated ladders are 1-1/4" sand-coated Epoxiglas

Dimensions

Diameter	2.5 in
Diameter - Hook	18 in
Dimensions	192 in x 27 in x 252 in
Dimensions Metric	487.7 mm x 68.6 mm x 640.1 mm
Height	252 in
Height Metric	640.1 mm
Length	192 in
Length Metric	487.7 mm
Side Rail Space	15 in
Weight	258 lb
WeightMetric	117 kg
Width	27 in
WidthMetric	68.6 mm

Product Assets

- [Installation Manuals - CHANCE® Tools Manuals](#)
- [Literature - Transmission Project Tools and Equipment Checklist](#)
- [Sales Drawings - SA_H4905](#)

General

EU RoHS Indicator	No
Strength Rating - Ultimate	750 lb
Style	Swivel Hook Ladder
UPC	096359371151



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CLTE-H490516B-SPEC-EN | REV 6/2024