



1.75" Square Shaft Extension(SS175), 3-1/2ft

By CHANCE Foundation Solutions
Catalog # [C1500183](#)

SS175, 42" long no helix.



Features

- Finish: Galvanized
- Capacity of helical pile can be determined by measuring installation

Application

Helical Anchoring

General

Coating	Hot Dip Galvanized
Holding Capacity Soil (Kt)	10
Shaft Type	SS
Torque Rating	10500 ft-lbs
Type	Anchor Extensions
UPC	096359012245

Dimensions

Length	40.50 in
Length - Effective	36.80 in
Weight	37.60 lb

Certifications and Compliance

CCMC Compliant?	CCMC 13193-R
ICC-ES Evaluated	ESR 2794
LARR Certified?	RR 25984

Logistics

Pallet Quantity 24

Product Assets

- Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure (BR04146E)
- Catalogs - CHANCE Helical Solutions Product Catalog (CA04140E)
- Engineering Drawing - SS175 Extensions
- ISO Certificates - Centralia_Operations_ISO_9001_2015
- Literature - New Construction Helical Pile Foundation System (SF04215E_0419)
- Literature - CHANCE® Building Code Evaluated Products December 2022
- Literature - Square Shaft Efficient Helical Pile Design (BR04326E)
- Sales Drawings - SS175 Extensions
- SDS - MSDS - Galvanized Steel Products
- Test Documents - ICC Evaluation (NER2794)

Related Products

- [C3030195](#)
- [055591P](#)
- [P0011443P](#)



A proud member of the Hubbell Family.