

Ground Clamp - All Angle Mounted 6' II-B-5

By Chance Lineman Tools & Equipment
Catalog # [HG422816SJ](#)

GROUND CLAMP - ALL ANGLE, 6FT -II-B-5, All-Angle.



Features

- All-Angle Grounding Clamps
- Aluminum Bodies with Serrated Jaws
- For installation ease, jaws pivot 75° left or right.
- Tapped for 5/8-11 UNC threaded ferrule

General

EU RoHS Indicator	No
Eye Screw/T-Handle	250 in-lb
Installation Torque (in-lb)	
Ferrule Installation Torque (in-lb)	250 in-lb
Handle Type	Hotstick
Jaw Type	Serrated Jaws
Material	Aluminum
Terminal Connection Type	Pressure
UPC	096359038771

Dimensions

Jaw Opening Size - Maximum	2.88 in
Jaw Opening Size - Minimum	.258 in
Length	6 in
Weight	5.145 lb

Electrical Ratings

Current Rating	400 A
Fault Current - 15 Cycles	43000 A
Fault Current - 30 Cycles	30000 A
Grounding Wire Capacity Maximum	4/0 Cable w/ Plain Terminal
Grounding Wire Capacity Minimum	#2 Cable w/ Plain Terminal

Certifications And Compliance

Fault Current - ASTM Grade	ASTM Grade 5
----------------------------	--------------

Product Assets

[Catalogs - Grounding Equipment](#)



A Hubbell brand