



2.875" Round Shaft Extension (RS2875.276), 10ft High Capacity Pile

By CHANCE Foundation Solutions
Catalog # [C2788383](#)



RS2875.276, 120" long Extension High Capacity Pile

Features

- Finish: Galvanized
- ICC-ES Approved Seismic Categories A-F
- Capacity can be determined by measuring installation torque

Application

Helical Anchoring

General

Coating	Galvanized
Finish Type	Galvanized
Holding Capacity Soil (Kt)	9
Shaft Type	RS
Torque Rating	10500 ft-lbs
Type	Anchor Extensions

Dimensions

Length	120.00 in
Length - Effective	120 in
Pipe Wall Thickness	0.276
Weight	78.2 lb

Product Assets

[Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure \(BR04146E\)](#)
[Literature - New Construction Helical Pile Foundation System \(SF04215E_0419\)](#)
[Literature - Round Shaft Helical Piles \(BR04314E\)](#)
[Sales Drawings - Leads And Extensions Rs2875.276 High Capacity Pile](#)
[SDS - MSDS - Galvanized Steel Products](#)

Related Products

[C2788381 - 2.875" Round Shaft Extension \(RS2875.276\), 5ft High Capacity Pile](#)
[P0011971P](#)
[C2788382 - 2.875" Round Shaft Extension \(RS2875.276\), 7ft High Capacity Pile](#)
[450315P](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CN-C2788383-SPEC-EN | REV 1/2024