

# 1 Ton Hotstick Handle Nylon-Strap Ratchet Hoist

By Chance Lineman Tools & Equipment  
Catalog # [PSC3090467](#)

Every Chain Hoist is proof-tested and factory-operated at 150% of capacity rating

## Features

- Always use with insulated link sticks of appropriate length
- Swivel-eye on handle end for operation via hot-line toos
- Hotstick rings on hooks and latches
- 1-Ton models use single-strap which allows for 5'9" Standard lift distance
- 27" minimum between hooks

## General

|                            |                 |
|----------------------------|-----------------|
| Catalog Number             | PSC3090467      |
| EU RoHS Indicator          | No              |
| Strength Rating - Ultimate | 2000 lb         |
| Style                      | Hotstick Handle |
| UPC                        | 096359391111    |
| Working Load Limit         | 2,000 lb        |
| Working Load Limit Metric  | 907 kg          |

## Dimensions

|                   |                             |
|-------------------|-----------------------------|
| Dimensions        | 22 in x 8.38 in x 5 in      |
| Dimensions Metric | 55.9 mm x 21.3 mm x 12.7 mm |



|               |         |
|---------------|---------|
| Height        | 5 in    |
| Height Metric | 12.7 mm |
| Length        | 22 in   |
| Length Metric | 55.9 mm |
| Weight        | 17.1 lb |
| WeightMetric  | 7.8 kg  |
| Width         | 8.38 in |
| WidthMetric   | 21.3 mm |

## Certifications And Compliance

|                          |                      |
|--------------------------|----------------------|
| Buy America(n) Qualified | Contact Manufacturer |
|--------------------------|----------------------|

## Logistics

|                  |   |
|------------------|---|
| Standard Package | 1 |
|------------------|---|

## Product Assets

[Catalogs - Load Handling Accessories](#)  
[Catalogs - Mechanical Hoists](#)  
[Installation Manuals - Strap Hoist Instruction Manual](#)  
[Specifications - PSC3090467](#)